





## NOTES:

1. LABEL PER ILS-100-05 (FOR INTERNAL USE ONLY)
LABEL LOCATION SHOWN FOR REFERENCE ONLY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

<b>V</b>		Š	× × × × × × × × × × × × × × × × × × ×		UNL
CAGE CODE	ALL DI	X=±.2 [5.08] FRACTIONS XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES±1°		TOLER	ESS OTHE
ת ח	MENSIONS SHO	; ; ;	FRACTIONS ± 1/32 ANGLES + 1°	TOLERANCES:	DIMENSIONS
DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	L ≤ 12 [305] = +1 [25] / 0  12 [305] < L ≤ 60 [1524] = +2 [51] / 0  60 [1524] < L ≤ 120 [3048] = +4 [102] / 0  120 [3048] < L ≤ 300 [7620] = +6 [152] / 0  300 [7620] < L = +5%L / 0		CABLE LENGTH (L) TOLERANCES:	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS
FMANED1031	NCE ONLY.			(L) TOLERANCES:	
	SCALE N/A	DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FARRVIEW MICROWAVE CORPOPATION ALL RIGHTS RESERVED. SHEET  OF  1  THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF ALL RIGHTS RESERVED.  SHEET  OF  1		THE INFORMATIO	THIRD-ANGLE PROJECTION
<b>&gt;</b>	P	_	CUMENT TY OF ORPORATION. ERVED.	N AND	-L