


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/08/2022	SPONG



- NOTES:
- ITEM IS MARKED WITH ITEM NUMBER WHERE SHOWN.
 "-XX" DENOTES THE ATTENUATION VALUE,
 EXAMPLE: 7448-3 = 3dB, 7448-10 = 10dB, ETC.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="0"> <tr> <td>X = ±.2</td> <td>[.008]</td> <td>FRACTIONS</td> <td>± 1/32</td> </tr> <tr> <td>XX = ±.02</td> <td>[.51]</td> <td></td> <td></td> </tr> <tr> <td>XXX = ±.005</td> <td>[.13]</td> <td>ANGLES ± 1°</td> <td></td> </tr> </table>		X = ±.2	[.008]	FRACTIONS	± 1/32	XX = ±.02	[.51]			XXX = ±.005	[.13]	ANGLES ± 1°		<p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.</p>	
X = ±.2	[.008]	FRACTIONS	± 1/32												
XX = ±.02	[.51]														
XXX = ±.005	[.13]	ANGLES ± 1°													
<p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>		SCALE	N/A												
SIZE	GAGE CODE	DRAWN BY	ITEM NO.												
A	3FKRS	AKRESOWSK	FMAT7448												
<p>CABLE LENGTH (L) TOLERANCES:</p> <table border="0"> <tr> <td>L ≤ 12 [305]</td> <td>± .125 [/-0]</td> </tr> <tr> <td>12 [305] < L ≤ 60 [1524]</td> <td>± .25 [/-0]</td> </tr> <tr> <td>60 [1524] < L ≤ 120 [3048]</td> <td>± .5 [102] [/-0]</td> </tr> <tr> <td>120 [3048] < L ≤ 300 [7620]</td> <td>± .6 [152] [/-0]</td> </tr> <tr> <td>300 [7620] < L</td> <td>± .5% [L / -0]</td> </tr> </table>		L ≤ 12 [305]	± .125 [/-0]	12 [305] < L ≤ 60 [1524]	± .25 [/-0]	60 [1524] < L ≤ 120 [3048]	± .5 [102] [/-0]	120 [3048] < L ≤ 300 [7620]	± .6 [152] [/-0]	300 [7620] < L	± .5% [L / -0]	SHEET	OF		
L ≤ 12 [305]	± .125 [/-0]														
12 [305] < L ≤ 60 [1524]	± .25 [/-0]														
60 [1524] < L ≤ 120 [3048]	± .5 [102] [/-0]														
120 [3048] < L ≤ 300 [7620]	± .6 [152] [/-0]														
300 [7620] < L	± .5% [L / -0]														
		1	1												

TITLE