



LABEL

.79 [20.0]

.37 [9.5]

.94 [24.0]

DV2106 YYWW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

MICTOWAVE⁷¹⁴

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.



an INFINIT® brand

TITLE

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. FRACTIONS ± 1/32 ANGLES ± 1° DRAWN BY K.DANG L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES: ITEM NO. FMDV2106 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICHOWAVE CORPORATION.
ALL RIGHTS RESERVED. N/A REV

 $X = \pm .2$ [5.08] $XX = \pm .02$ [.51] $XXX = \pm .005$ [.13]

N SIZE

CAGE CODE 3FKR5