


## WR-19 WAVEGUIDE UG-383/U-M ROUND COVER FLANGE



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO.S. LAW PROHIBITED.

MICTOWAVE

\*\*UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES

| MICTOWAVE

\*\*UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES

| DIMENSIONS IN [] ARE MILLIMETERS



an INFINIT® brand

TITLE

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. FRACTIONS ± 1/32 ANGLES ± 1° L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES: THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED. N/A

 $X = \pm .2$  [5.08]  $XX = \pm .02$  [.51]  $XXX = \pm .005$  [.13]

TOLERANCES:

NGLE PROJECTION

A

CAGE CODE 3FKR5

DRAWN BY
K.DANG

ITEM NO.

FMW19FS2

REV