



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

	.XX = ±.02 [.51] ± 1/32 .XXX = ±.005[.13] ANGLES ± 1°	X=±2 [5.08] FRACTIC XX=±.02 [.51] ±1/32 XXX=±.005[.13] ANGLES	X = ±.2 [5.08] FRACTIC XX = ±.02 [.51] ± 1/3.2 XXX = ±.005[.13] ANGLES
300 76301	60 [1524] < L \le 120 [3048] = +4 [102] / -0 120 [3048] < L \le 300 [7620] = +6 [152] / -0	L ≤ 12 (305) = +1 (25) / 0 12 (305) < L ≤ 60 (1524) = +2 (51) / 0 (1524) < L ≤ 120 (3048) = +4 (102) / 0 (3048) < L ≤ 300 (7620) = +6 (152) / 0	CABLE LENGTH (L) TOLERANCES: L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 80 [1824] = +2 [51] / 0 10 [1824] < L ≤ 120 [3048] = +4 [102] / 0 10 [3048] < L ≤ 300 [7820] = +6 [182] / 0
	\neg	FAIRVIE	
	ORE	DPER AVE OF	WATION HIS DOC OPERT AVE CC S RESE