



WR28	Inches	mm
Dimension		
A	0.500	12.70
H	0.750	19.05
J	0.530	13.46
K ( $\pm 0.010$ )	0.280	7.11
L ( $\pm 0.010$ )	0.140	3.56
AA	0.105	2.67
AB	3.125	79.38
AC	1.095	27.81
AD	1.450	36.83



BACK VIEW

STANDARD TOLERANCES	
.X	$\pm 0.2$
.XX	$\pm 0.1$
.XXX	$\pm 0.05$

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

# FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

TITLE		DWG NO		CAGE CODE	
		SH128-20		3FKR5	
CAD FILE	120816	SHEET		SCALE	N/A
				SIZE	A
					41742