











4X Ø .116 [2.95] ▼ THRU HOLES

.280±.001 [7.11±0.03]

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

an INFINIT® brand

A V		XX X X X X X X X X X X X X X X X X X X		UNL
3FX	ALL DIN	X = ±.2 [5.08] XX = ±.02 [.51] XXX = ±.005[.13]	TOLERANCES:	ESS OTHER
3FXR5	ENSIONS SH	FRACTIONS ± 1/32 ANGLES ± 1°	NCES:	RWISE SPECIF
K DANG	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY		CABLE LENGTH (L) TOLERANCES:	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS
ITEM NO.	NCE ONLY.	L ≤ 12 [305] = +1 [25] / 0 12 [305] < L ≤ 60 [1824] = +2 [51] / 0 60 [1824] < L ≤ 120 [3048] = +4 [102] / 0 120 [3048] < L ≤ 300 [7620] = +6 [152] / 0 300 [7620] < L = +5%L / 0	(L) TOLERANCES:	ONS ARE INCHES
SMW28TW1001 REV	SCALE N/A	FAIRVIE	THE INFORMATION AND	THIRD-ANGLE PROJECTION