



MCX/M-MCX/M FLEXIBLE CABLES 3GHZ RG316

FMC0707315-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: 1.2 dB MAX @ 3GHZ

RAW CABLE: RG316
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHZ: 0.26 DB/FT
@2GHZ: 0.38 DB/FT
@3GHZ: 0.47 DB/FT


OUTER SHIELD DIAMETER: .098"

CONNECTORS:
MCX:
MATERIAL BODY: BRASS
CENTER CONTACT: BRASS
CONTACT PLATING: Au MIL-G-45204
INSULATOR: TEFLON

OP TEMP: -55°C to +105°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE
MCX/M-MCX/M FLEXIBLE CABLES 3GHZ RG316

SIZE A	CAGE CODE 3FKR5	DWG NO FMC0707315-XX	REV --
SCALE		SHEET	

