

FMCA2263 DATA SHEET

NEX10 Male to NEX10 Female Bulkhead Cable 1/4 inch Superflexible Coax

The NEX10 male to NEX10 female bulkhead cable using 1/4 inch superflexible coax, part number FMCA2263, from Fairview Microwave is in-stock and ships same day. This Fairview NEX10 to NEX10 cable assembly has a male to female gender configuration with 50 ohm corrugated 1/4" superflexible coax. Fairview Microwave's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. The FMCA2263 NEX10 male to NEX10 female cable assembly operates to 6 GHz. Our RF cable assembly with NEX10 bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	T	ур	Max	U	nits
Frequency Range	DC			6	(GHz
VSWR				1.5:1		
Velocity of Propagation		8	32			%
RF Shielding	120				(dB
Passive Intermodulation				-150	C	lBc

Capacitance		24.4 [80.05]		pF/ft [pF/m]
Inductance		0.059 [0.19]		uH/ft [uH/m]
DC Resistance Inner Cor	3.2 [10.5]		Ω/1000ft [Ω/Km]	
DC Resistance Outer Cor	nductor	2.53 [8.3]		Ω/1000ft [Ω/Km]
Jacket Spark			2,000	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.016	0.026	0.039	0.057	0.107	dB/ft
	0.05	0.09	0.13	0.19	0.35	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2dB connector loss.

Mechanical Specifications

Cable Assembly

Diameter

0.62 in [15.75 mm]



Configuration:

- NEX10 Male
- NEX10 Female Bulkhead
- 1/4" Superflexible

Features:

- Max Frequency 6 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable

Applications:

- General Purpose
- Laboratory Use
- Distributed Antenna Systems (DAS)
- Low PIM Applications and PIM Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Cable

Cable Type 1/4" Superflexible Impedance 50 Ohms

Inner Conductor Type Solid

Inner Conductor Material and Plating Copper Clad Aluminum

Dielectric Type PE (F)
Number of Shields 1

Shield Layer 1 Helically Corrugated Copper Tube

Jacket Material PE, Black

Jacket Diameter 0.303 in [7.7 mm]

One Time Minimum Bend Radius 0.5 in [12.7 mm]
Repeated Minimum Bend Radius 1 in [25.4 mm]

Typical Flex Cycles 2

Tensile Strength 79 lbs [35.83 Kg]

Connectors

Description	Connector	1 Connecto	r 2
Туре	NEX10 Male	e NEX10 Fem	nale
Mount Method		Bulkhead	d
Specification	NEX10	NEX10	
Impedance	50 Ohms	50 Ohm	S
Contact Material & Plating	Brass, Silver	r	
Dielectric Type	PTFE	PTFE	
Outer Cond Material & Plati	ing	Bronze, Silv	ver
Body Material & Plating	Brass, Tri-Met	tal Brass, Tri-M	etal

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration: FMCA2263 - xx uu

cm = Centimeters

Length

Example: FMCA2263-12 = 12 inches long cable

FMCA2263-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





NEX10 Male to NEX10 Female Bulkhead Cable 1/4 inch Superflexible Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: NEX10 Male to NEX10 Female Bulkhead Cable 1/4 inch Superflexible Coax FMCA2263

URL: https://www.fairviewmicrowave.com/nex10-male-nex10-female-pe-1-4-sfhc-cable-assembly-FMCA2263-p.aspx







