



### VITA 67 Mini SMP Female to 2.92mm Female Cable FM-F086HF Coax

## 

### **FMCA9743**

### Configuration

· Connector 1: Mini SMP Female · Connector 2: 2.92mm Female Cable Type: FM-F086HF · Coax Cable Group: 2

· Coax Flex Type: Flexible

### **Features**

- · Max Frequency 40 GHz
- Shielding Effectivity > 110 dB
- 70% Phase Velocity
- · Standard MIL-STD-348 SMPM interface
- · Push-on/snap-on mating style for quick installation
- · Mini SMP (SMPM) Female compatible with VITA 67 (4-port) and (8-port) blocks
- Mini SMP (SMPM) Male Compatible with VITA 67 (4-port) and (8port) blocks

### **Applications**

- · General Purpose
- Laboratory Use
- · Scientific research

- High-reliability, high-density for aerospace Ground base station & communication & defense application
  - systems, avionics, radar systems

### **Description**

The Mini SMP female to 2.92mm female cable using FM-F086HF coax, part number FMCA9743, from Fairview Microwave is in-stock and ships same day. This Fairview Mini SMP to 2.92mm cable assembly has a female to female gender configuration with 50 ohm flexible coax. Fairview Microwave's VITA 67 assemblies are high-density, high-performance RF cable assemblies that fit into VITA 67 blocks and attach to the PCB board which makes it ideal for applications where tight bends and flexure is required. The FMCA9743 Mini SMP female to 2.92mm female cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.45:1	
Velocity of Propagation		70		%
RF Shielding	110			dB



### VITA 67 Mini SMP Female to 2.92mm Female Cable FM-F086HF Coax

# 

### **FMCA9743**

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Capacitance		29.4 [96.46]		pF/ft [pF/m]

### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	40	GHz
Insertion Loss (Typ.)	0.344	0.503	0.743	1.048	1.703	dB/ft
	1.13	1.65	2.44	3.44	5.59	dB/m

Electrical Specification Notes: Values at 25°C, sea level.

### **Mechanical Specifications**

Cable Assembly

Weight 0.31 lbs [140.61 g]

Cable

Cable TypeFM-F086HFImpedance50 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Copper Clad Steel, Silver

Dielectric Type PTFE

Shield Layer 1 Silver Plated Copper Tape

### **Connectors**

Description	Connector 1	Connector 2
Туре	Mini SMP Female	2.92mm Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Nickel
Contact Plating Specification	ASTM B488	50 μin minimum
Body Material and Plating	Beryllium Copper, Gold	Passivated Stainless Steel
Body Plating Specification	ASTM B488	SAE-AMS-2700

### **Environmental Specifications**

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:





### VITA 67 Mini SMP Female to 2.92mm Female Cable FM-F086HF Coax

### 

### **FMCA9743**

Values at 25°C, sea level.

### **Typical Performance Data**

### **How to Order**

Part Number Configuration: **FMCA9743** - XX uu - Unit of Measure: cm = Centimeters <blank> = Inches Length Base Number

Example: FMCA9743-12 = 12 inches long cable FMCA9743-100cm = 100 cm long cable

VITA 67 Mini SMP Female to 2.92mm Female Cable FM-F086HF Coax from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: VITA 67 Mini SMP Female to 2.92mm Female Cable FM-F086HF Coax FMCA9743

URL: https://www.fairviewmicrowave.com/vita-67-mini-smp-female-to-2.92mm-female-cable-fm-f086hf-coax-fmca9743-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

