

FMCN1361 DATA SHEET

MHV Female Bulkhead Connector Solder Cup Terminal Solder Attachment , .380 inch DD Hole

MHV female bulkhead connector with solder cup terminal (.380 inch DD hole), part number FMCN1361, from Fairview Microwave is in-stock and ships same day. This MHV female connector operates up to a maximum frequency of 300 MHz and offers excellent VSWR of 1.2:1. Fairview's FMCN1361 bulkhead MHV connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's MHV female bulkhead connector FMCN1361 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		300	MHz
VSWR			1.2:1	
Operating Voltage (AC)			3,500	Vrms
Inner Cond. DC Resistance)		2	mOhms
Outer Cond. DC Resistanc	е		1.5	mOhms

Mechanical Specifications

Size	
Length	1.69 in [42.93 mm]
Width/Dia.	0.57 in [14.48 mm]
Weight	0.027 lbs [12.25 g]

Material Specifications

Description	Material	Plating	
Contact	Brass	Gold 30 µin minimum	
Insulation	PTFE		
Outer Conductor	Brass	Nickel 100 µin minimum	
Body	Brass	Nickel 100 µin minimum	



Configuration:

- MHV Female Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- Solder Cup Interface Type
- Solder Attachment
- Bulkhead

Features:

- Operating Frequency of 300 MHz Max.
- Excellent VSWR of 1.2:1
- Gold Plated Brass Contact
- 30 µin minimum contact plating

Applications:

- General Purpose Test
- Rack and Panel Mount Applications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

-55 to +155 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

Assembly Instruction

MHV Female Bulkhead Connector Solder Cup Terminal Solder Attachment , .380 inch DD Hole from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: MHV Female Bulkhead Connector Solder Cup Terminal Solder Attachment , .380 inch DD Hole FMCN1361

URL: https://www.fairviewmicrowave.com/mhv-female-solder-cup-terminal-connector-fmcn1361-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689