

3 Way Power Divider SMA Connectors From 1 GHz to 2 GHz Rated at 30 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, 2.4mm, 1.85mm BNC, N and SMA.

The FMDV1102 is a 3-way power divider that operates from 1 to 2 GHz and can handle up to 30 Watts (CW) with 0.6 dB max insertion loss and 20 dB min isolation. The package interface uses SMA female connectors.

Electrical Specifications

Number of Output Ports			3	
Description	Min	Typ	Max	Units
Frequency Range	1		2	GHz
Impedance		50		Ohms
Input VSWR		1.25:1	1.3:1	
Output VSWR		1.2:1	1.3:1	
Insertion Loss		0.4	0.6	dB
Isolation	20	22		dB
Amplitude Balance		0.2	0.3	dB
Phase Balance		4	5	Degrees
Nominal Power Splitting		4.8		dB
Input Power (CW)			30	Watts
Reverse Power (CW)			2	Watts
Input Power (Peak) 10% Duty Cycle 1us Pulse Width			300	Watts

Mechanical Specifications

Size	
Length	1.6 in [40.64 mm]
Width	2.03 in [51.56 mm]
Height	0.39 in [9.91 mm]
Weight	0.12 lbs [54.43 g]
Housing Material and Plating	Aluminum
Configuration	
Package Type	Connectorized
Input Connector	SMA Female
Output Connectors	SMA Female

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C



Features:

- 3-Way Power Divider
- SMA Female Connectorized Design
- 1 to 2 GHz Frequency Range
- Max Power 30 Watts (CW)
- Insertion Loss < 0.6 dB
- Isolation > 20 dB

Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Humidity
Shock
Vibration
Altitude

100% RH at 35°C, 95%RH at 40°C
20G for 11msec half sine wave, 3 axis both directions
25gRMS (15 degrees 2KHz) endurance, 1 hour per axis
30,000 ft. (Epoxy Sealed Controlled environment)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

3 Way Power Divider SMA Connectors From 1 GHz to 2 GHz Rated at 30 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [3 Way Power Divider SMA Connectors From 1 GHz to 2 GHz Rated at 30 Watts FMDV1102](#)

URL: <https://www.fairviewmicrowave.com/3-way-power-divider-sma-2-ghz-fmdv1102-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

