

BNC F'S POWER DIVIDER .2-1000 MHZ

MP021000-2

SPECIFICATIONS

ELECTRICAL


FREQUENCY: .2-1000 MHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.5:1 MAX
 INSERTION LOSS: 1.2 DB MAX
 INPUT POWER(MAX) : 1 WATT
 ISOLATION: 18 DB MIN

MECHANICAL


MATERIAL CONNECTORS: NICKEL PLATED BRASS
 MATERIAL CONTACTS: Au PLATED BeCu

OPERATING TEMPERATURE: -25°C TO +80°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC F'S POWER DIVIDER .2-1000 MHZ

SIZE A	CAGE CODE 3FKR5	DWG NO MP021000-2	REV A
------------------	---------------------------	-----------------------------	-----------------

SCALE

SHEET