



RA SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable

RA SMP female connector with solder/solder attachment for RG405, RG405 Tinned and .086 SR, part number SC5233, from Fairview Microwave is in-stock and ships same day. This SMP female connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.25:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA SMP female connector SC5233 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.25:1	

Mechanical Specifications

 Size
 Length
 0.265 in [6.73 mm]

 Width/Dia.
 0.131 in [3.33 mm]

 Height
 0.128 in [3.25 mm]

 Weight
 0.0045 lbs [2.04 g]

Material Specifications

Description	Material	Plating		
Contact	Beryllium Copper	Gold MIL-G-45204		
Insulation	PTFE			
Outer Conductor	Beryllium Copper	Gold MIL-G-45204		

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- SMP Female Connector
- MIL-STD-348
- 50 Ohms
- Right Angle Body Geometry
- RG405, RG405 Tinned, .086 SR Interface Type
- Solder/Solder Attachment

Features:

- Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.25:1
- Blind Mate Connector
- Gold Plated Beryllium Copper Contact
- Contact plating according to MIL-G-45204

Applications:

- General Purpose Test
- · Custom Cable Assemblies

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairyiewmicrowaye.com






Assembly Instruction

RA SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001: 2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RA SMP Female Connector Solder Attachment For RG405, RG405 Tinned, .086 SR Cable SC5233

URL: https://www.fairviewmicrowave.com/smp-female-standard-rg405-connector-sc5233-p.aspx









STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

- 1. STRIP CABLE AS SHOWN & SHARP CENTER CONDUCTOR.
- 2. INSERT CABLE INTO BODY UNTIL IT SITS IN PLACE.
- 3. SOLDER OUTER CONDUCTOR TO BODY. PRESS DOWN CAP.

STANDARD TOLERANCES

.X ±0.2 .XX ±0.1

XXX ±0.1

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RA SMP Female Connector Solder Attachment For	DWG NO SC5233			CAGE CODE 3FKR5		
RG405, RG405 Tinned, .086 SR Cable	CAD FILE 062617	SHEET	SCAL	E N/A	SIZE A	2233