

SMA Male to SSMA Male Cable RG-405 Coax

The SMA male to SSMA male cable using RG-405 coax, part number SCA71086, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SSMA cable assembly has a male to male gender configuration with 50 ohm flexible RG-405 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The SCA71086 SMA male to SSMA male cable assembly operates to 12.4 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12.4	GHz

Mechanical Specifications

Cable Assembly
Length*

0 in [0 mm]

Cable
Cable Type
Impedance
Dielectric Type

RG-405
50 Ohms
PTFE

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SSMA Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Outer Cond Material & Plating	Stainless Steel, Gold	Stainless Steel, Gold
Coupling Nut Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Configuration:

- SMA Male
- SSMA Male
- RG-405

Features:

- Max Frequency 12.4 GHz

Applications:


- General Purpose
- Laboratory Use

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

How to Order

Part Number Configuration:

SCA71086 - xx uu




Example: SCA71086-12 = 12 inches long cable
SCA71086-100cm = 100 cm long cable

SMA Male to SSMA Male Cable RG-405 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMA Male to SSMA Male Cable RG-405 Coax SCA71086](#)


URL: <https://www.fairviewmicrowave.com/sma-male-ssma-male-cable-rg-405-coax-sca71086-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
	DWG NO SCA71086			CAGE CODE 3FKR5				
	CAD FILE	01/23/19	SHEET	1 OF 1	SCALE	N/A	SIZE	A
TITLE SMA Male to SSMA Male Cable RG-405 Coax								