



2.4mm Female to 2.4mm Female Bulkhead Adapter

2.4mm female to 2.4mm female bulkhead adapter part number SM3015 from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm adapter has a female to female gender configuration. SM3015 2.4mm female to 2.4mm female adapter operates to 50 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors. Our RF 2.4mm to 2.4mm bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		50	GHz
VSWR			1.3:1	

Electrical Specification Notes:

Values at 25°C, sea level.

Mechanical Specifications

Size Length Weight

0.843 in [21.4 mm] 0.0155 lbs [7.03 g]

Description	Connector 1	Connector 2	
Туре	2.4mm Female	2.4mm Female	
Polarity	Standard	Standard	
Mating Cycles	500	500	

Material Specifications

Description	Connector 1	Connector 2	
Туре	2.4mm Female	2.4mm Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold over Nickel	Gold over Nickel	
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Insulation Material	Oxide-Noryl	Oxide-Noryl	
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel	
Outer Contact Plating Spec.	ASTM A380	ASTM A380	



Configuration:

- 2.4mm Female Connector 1
- 2.4mm Female Connector 2
- 50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.3:1 max up to 50 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature

Operating Range Vibration Salt Spray -55 to +100 deg C MIL-STD 202, Method 204, Condition D (20 G's) MIL-STD 202, Method 101, Condition B, 5% salt solution


Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data









2.4mm Female to 2.4mm Female Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.4mm Female to 2.4mm Female Bulkhead Adapter SM3015

URL: https://www.fairviewmicrowave.com/2.4mm-female-2.4mm-female-bulkhead-adapter-sm3015-p.aspx







