

SM3311 DATA SHEET

3.5mm Female to 3.5mm Female 4 Hole Flange Adapter Threaded Through Holes

3.5mm female to 3.5mm female 4 hole flange adapter part number SM3311 from Fairview Microwave is in-stock and ships same day. This Fairview 3.5mm to 3.5mm adapter has a female to female gender configuration. SM3311 3.5mm female to 3.5mm female adapter operates to 34 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. The 3.5mm connector mates mechanically with commercially available SMA and 2.92mm (K) connectors. Our RF 3.5mm to 3.5mm 4 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		34	GHz
VSWR			1.3:1	

Electrical Specification Notes: Values at 25°C, sea level.

Configuration:

- 3.5mm Female Connector 1
- 3.5mm Female Connector 2
- 50 Ohm
- Straight Body Geometry
- 4 Hole Flange Mount Method

Features:

- VSWR of 1.3:1 max up to 34 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Mechanical Specifications

Size Length Width Weight

0.977 in [24.8 mm] 0.5 in [12.7 mm] 0.0141 lbs [6.4 g]

Description	Connector 1	Connector 2	
Туре	3.5mm Female	3.5mm Female	
Polarity	Standard	Standard	
Mating Cycles	500	500	

Material Specifications

Description	Connector 1	Connector 2		
Туре	3.5mm Female	3.5mm Female		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Gold over Nickel	Gold over Nickel		
Contact Plating Spec.	MIL-G-45204	MIL-G-45204		
Insulation Material	Rexolite	Rexolite		
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel		
Outer Contact Plating Spec.	ASTM A380	ASTM A380		

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature


Operating Range Vibration Salt Spray -55 to +100 deg C MIL-STD 202, Method 204, Condition D (20 G's) MIL-STD 202, Method 101, Condition B, 5% salt solution

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



3.5mm Female to 3.5mm Female 4 Hole Flange Adapter Threaded Through Holes from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 3.5mm Female to 3.5mm Female 4 Hole Flange Adapter Threaded Through Holes SM3311

URL: https://www.fairviewmicrowave.com/3.5mm-female-3.5mm-female-4-hole-flange-adapter-sm3311-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
3.5mm Female to 3.5mm Female 4 Hole Flange Adapter Threaded Through Holes	DWG NO SM3311		CAG	CAGE CODE 3FKR5	
	CAD FILE 111615	SHEET	SCALE N//	SIZE A	150