



Push-On SMA Male to SMA Female Bulkhead Adapter

Push-on SMA male to SMA female bulkhead adapter part number FMAD1031 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA adapter has a male to female gender configuration and is built of durable stainless steel. FMAD1031 SMA male to SMA female adapter operates to 18 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our RF SMA to SMA bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.25:1	
Operating Voltage (AC)			335	Vrms
DWV (AC)			750	Vrms
Inner Conductor DC Resistance			3	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 8	8 to 18				GHz
VSWR, Max	1.15:1	1.25:1				

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size

 Length
 0.795 in [20.19 mm]

 Width
 0.377 in [9.58 mm]

 Height
 0.377 in [9.58 mm]

 Weight
 0.015 lbs [6.8 g]

DescriptionConnector 1Connector 2TypeSMA MaleSMA FemaleConnection MethodPush-OnPolarityStandardStandard



Configuration:

- Push-On SMA Male Connector 1
- SMA Female Connector 2
- 50 Ohm
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- VSWR of 1.25:1 max up to 18 GHz
- SMA interface meets MIL-STD-348A
- 30 µin minimum contact plating
- · Gold over Nickel Plated Contact

Applications:

- · General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Interface Specification	MIL-STD-348A	MIL-STD-348A			
Mating Cycles	500	500			

Material Specifications

Description	Connector 1 Connector 2				
Туре	SMA Male	SMA Female			
Contact Material	Beryllium Copper	Beryllium Copper			
Contact Plating	Gold over Nickel	Gold over Nickel			
Contact Plating Spec.	30 µin minimum	30 μin minimum			
Insulation Material	PTFE	PTFE			
Outer Contact Material	Beryllium Copper				
Outer Contact Plating	Gold over Nickel				
Outer Contact Plating Spec.	3 µin minimum				
Body Material	Passivated Stainless Steel	Passivated Stainless Steel			

Environmental Specifications

Temperature

Operating Range Vibration Salt Spray -65 to +165 deg C MIL-STD-202, Method 204, Condition D MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:









Push-On SMA Male to SMA Female Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Push-On SMA Male to SMA Female Bulkhead Adapter FMAD1031

URL: https://www.fairviewmicrowave.com/push-on-sma-male-sma-female-bulkhead-adapter-fmad1031-p.aspx









FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Push-On SMA Male to SMA Female Bulkhead Adapter	DWG NO CAGE COD				3FKR5	
	CAD FILE 022715	SHEET	SCAL	E N/A	SIZE A	150