



Low PIM 4.3-10 Female to 4.3-10 Female Adapter

4.3-10 female to 4.3-10 female adapter part number FMAD1096 from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 adapter has a female to female gender configuration in a low PIM design. FMAD1096 4.3-10 female to 4.3-10 female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.08:1 maximum and passive intermodulation of -166 dBc maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.08:1	
Insertion Loss			0.13	dB
Passive Intermodulation			-166	dBc
Operating Voltage (AC)			1,000	Vrms
DWV (AC)			2,500	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size	
Length	
Width	
Weight	

1.45 in [36.83 mm] 0.78 in [19.81 mm] 0.113 lbs [51.26 q]

Description	Connector 1	Connector 2
Туре	4.3-10 Female	4.3-10 Female
Polarity	Standard	Standard
Mating Cycles	100	100
Contact Retention Force, Min	6 lbs [2.72 Kg]	6 lbs [2.72 Kg]



Configuration:

- 4.3-10 Female Connector 1
- 4.3-10 Female Connector 2
- 50 Ohm
- · Low PIM Design
- Straight Body Geometry

Features:

- VSWR of 1.08:1 max up to 6 GHz
- PIM levels better than -166 dBc
- Silver Plated Bronze Contact
- · Low Coupling Torque
- Corrosion Resistant Tri-Metal Finish

Applications:

- General Purpose Test
- Low PIM Applications
- Mobile Communications Systems
- Base Stations
- Distributed Antenna Systems (DAS)
- Small Cells
- Feeder Cables

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2		
Туре	4.3-10 Female	4.3-10 Female		
Contact Material	Bronze	Bronze		
Contact Plating	Silver	Silver		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Bronze	Bronze		
Outer Contact Plating	Silver	Silver		
Body Material	Brass	Brass		
Body Plating	Tri-Metal	Tri-Metal		

Environmental Specifications

Temperature

Operating Range

-55 to +90 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Low PIM 4.3-10 Female to 4.3-10 Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Low PIM 4.3-10 Female to 4.3-10 Female Adapter FMAD1096

URL: https://www.fairviewmicrowave.com/low-pim-4.3-10-female-4.3-10-female-adapter-fmad1096-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2017

REV 1.0 Page 2 of 3







STANDARD TOLERANCES

.X ±0.2 .XX ±0.1 .XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Low PIM 4.3-10 Female to 4.3-10 Female Adapter	DWG NO CAGE CODE SFKR5			FKR5		
	CAD FILE 102616	SHEET	SCALI	E N/A	SIZE A	2233