

Precision TNC Male (Plug) to TNC Female (Jack) Adapter, Passivated Stainless Steel Body, 1.15 VSWR

TNC male to TNC female adapter part number FMAD1239 from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC adapter has a male to female gender configuration in a precision design. FMAD1239 TNC male to TNC female adapter operates to 18 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.15:1 maximum. Our TNC to TNC RF adapter can also be used as a connector saver to extend equipment life.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		18	GHz
VSWR			1.15:1	
Insertion Loss			0.22	dB

Electrical Specification Notes: Values at 25°C, sea level. Insertion Loss (dB) = 0.05*sqrt(fGHz).

Mechanical Specifications

Size Length Width		1.031 in [26.2 mm] 0.625 in [15.88 mm]
Description	Connector 1	Connector 2
Туре	TNC Male	TNC Female
Polarity	Standard	Standard
Mating Cycles	500	
Hex Size	9/16 in.	

Material Specifications

Description	Connector 1	Connector 2	
Туре	TNC Male	TNC Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold over Nickel	Gold over Nickel	
Insulation Material	PTFE	PTFE	
Outer Contact Material		Passivated Stainless Steel	
Body Material	Passivated Stainless Steel		
Gasket Material	Silicone Rubber		
Coupling Nut Material	Passivated Stainless Steel		





Configuration:

- TNC Male Connector 1
- TNC Female Connector 2
- 50 Ohm
- Precision Design
- Straight Body Geometry

Features:

- VSWR of 1.15:1 max up to 18 GHz
- Gold over Nickel Plated
 Beryllium Copper Contact

Applications:

- Connector Saver
- General Purpose Test
- Precision Test & Measurement

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Precision TNC Male (Plug) to TNC Female (Jack) Adapter, Passivated Stainless Steel Body, 1.15 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Precision TNC Male (Plug) to TNC Female (Jack) Adapter, Passivated Stainless Steel Body, 1.15 VSWR FMAD1239

URL: https://www.fairviewmicrowave.com/precision-tnc-male-tnc-female-adapter-fmad1239-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689