

FMAD1260 DATA SHEET

Precision 3.5mm Female to 7mm Adapter with Passivated Stainless Steel Body

3.5mm female to 7mm adapter part number FMAD1260 from Fairview Microwave is in-stock and ships same day. This Fairview 3.5mm to 7mm adapter has a female to sexless gender configuration and is built of durable stainless steel in a precision design. FMAD1260 3.5mm female to 7mm adapter operates to 18 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.15:1 maximum. The 3.5mm connector mates mechanically with commercially available SMA and 2.92mm (K) connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.15:1	

Mechanical Specifications

Size

Length 1.527 in [38.8 mm]
Width 0.87 in [22.1 mm]

Connector 1	Connector 2	
3.5mm Female	7mm Sexless	
Standard	Standard	
	3.5mm Female	3.5mm Female 7mm Sexless

Material Specifications

Description	Connector 1	Connector 2	
Туре	3.5mm Female	7mm Sexless	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold over Nickel	Gold over Nickel	
Contact Plating Spec.	4µ in. minimum	4μ in. minimum	
Insulation Material	Oxide-Noryl	Oxide-Noryl	
Outer Contact Material	Passivated Stainless Steel		
Body Material	Passivated Stainless Steel	Passivated Stainless Steel	
Coupling Nut Material		Passivated Stainless Steel	

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- 3.5mm Female Connector 1
- 7mm Sexless Connector 2
- 50 Ohm
- Precision Design
- Straight Body Geometry

Features:

- VSWR of 1.15:1 max up to 18 GHz
- 4µ in. minimum contact plating
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test
- Precision Test & Measurement

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Precision 3.5mm Female to 7mm Adapter with Passivated Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Precision 3.5mm Female to 7mm Adapter with Passivated Stainless Steel Body FMAD1260

URL: https://www.fairviewmicrowave.com/precision-3.5mm-female-7mm-sexless-adapter-fmad1260-p.aspx







