



N Female to MCX Plug Adapter

Type N female to MCX plug adapter part number FMAD1302 from Fairview Microwave is in-stock and ships same day. This Fairview type N to MCX adapter has a female to plug gender configuration. FMAD1302 type N female to MCX plug adapter operates to 6 GHz.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
Operating Voltage (AC)			170	Vrms
DWV (AC)			500	Vrms
Insulation Resistance	1,000			MOhms

Mechanical Specifications

Size

 Length
 1.356 in [34.4 mm]

 Width
 0.625 in [15.88 mm]

Weight 0.0112 lbs [5.08 g]

Description	Connecto	r 1 Connector 2	
Туре	N Femal	e MCX Plug	
Polarity	Standard	d Standard	
Interface Specification	MIL-STD-3	348 MIL-C-39012	



Configuration:

- N Female Connector 1
- MCX Plug Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- Type N interface meets MIL-STD-348
- MCX interface meets MIL-C-39012
- Contact plating according to MIL-G-45204

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2	
Туре	N Female	MCX Plug	
Contact Plating	Gold	Gold	
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Insulation Material	PTFE	PTFE	
Outer Contact Material	Brass		
Outer Contact Plating	Nickel		
Outer Contact Plating Spec.	QQ-N-290		
Body Material		Brass	
Body Plating		Nickel	
Body Plating Spec.		QQ-N-290	
Coupling Nut Material		Brass	
Coupling Nut Plating		Nickel	
Coupling Nut Plating Spec.		QQ-N-290	

Environmental Specifications

TemperatureOperating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

N Female to MCX Plug Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: N Female to MCX Plug Adapter FMAD1302

URL: https://www.fairviewmicrowave.com/n-female-to-mcx-plug-adapter-fmad1302-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





