

Triax TRB 4 Lug Bulkhead Jack Feedthrough non-insulated Barrel Front Mount Panel Jack

Bulkhead INVALID ALIAS LOOKUP FOR *TRB 4-Lug* jack to INVALID ALIAS LOOKUP FOR *TRB 4-Lug* jack bulkhead adapter part number FMADMSB00006 from Fairview Microwave is in-stock and ships same day. This Fairview INVALID ALIAS LOOKUP FOR *TRB 4-Lug* to INVALID ALIAS LOOKUP FOR *TRB 4-Lug* adapter has a jack to jack gender configuration. FMADMSB00006 INVALID ALIAS LOOKUP FOR *TRB 4-Lug* jack to INVALID ALIAS LOOKUP FOR *TRB 4-Lug* jack adapter. Our RF INVALID ALIAS LOOKUP FOR *TRB 4-Lug* bulkhead to INVALID ALIAS LOOKUP FOR *TRB 4-Lug* bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Mechanical Specifications

Size	
Length	1.29 in [32.77 mm]
Width	0.73 in [18.54 mm]
Height	0.73 in [18.54 mm]
Weight	0.01 lbs [4.54 g]

Description	Connector 1	Connector 2
Type	TRB 4-Lug Jack	TRB 4-Lug Jack
Polarity	Standard	Standard
Interface Specification	MIL-STD-1553B	MIL-STD-1553B

Mechanical Specification Notes:
Isolated

Material Specifications

Description	Connector 1	Connector 2
Type	TRB 4-Lug Jack	TRB 4-Lug Jack
Insulation Material	PTFE	PTFE
Outer Contact Material	Beryllium Copper	Beryllium Copper
Outer Contact Plating	Gold	Gold
Body Material	Brass	Brass
Body Plating	Nickel	Nickel
Coupling Nut Material	Brass	Brass
Coupling Nut Plating	Nickel	Nickel

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Configuration:

- TRB 4-Lug Jack Connector 1
- TRB 4-Lug Jack Connector 2
- Straight Body Geometry
- Bulkhead Mount Method

Features:

- INVALID ALIAS LOOKUP FOR *TRB 4-Lug* interface meets MIL-STD-1553B
- Non-Isolated

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Triax TRB 4 Lug Bulkhead Jack Feedthrough non-insulated Barrel Front Mount Panel Jack from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Triax TRB 4 Lug Bulkhead Jack Feedthrough non-insulated Barrel Front Mount Panel Jack FMADMSB00006](#)

URL: <https://www.fairviewmicrowave.com/bulkhead-invalid-alias-lookup-for-trb-4-lug-jack-to-invalid-alias-lookup-for-trb-4-lug-jack-bulkhead-adapter-fmadmsb00006-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



