an INFINIT® brand

FMC0100214 DATA SHEET

N Male to Straight Cut Lead Cable RG-214 Coax

The 50 ohm type N male to straight cut lead cable using RG-214 coax, part number FMC0100214, from Fairview Microwave is in-stock and ships same day. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness. These N Male to unterminated flush cut cables assemblies are designed to be used as convenient test probes.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specificati					
Cable Assembly Diameter	0.787 in [19.99 mm]				
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Materi Dielectric Type	al and Plating	RG-214 50 Ohms Solid Copper, Sil PE	-		
Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter		2 Silver Plated Copper E Silver Plated Copper E PVC, Black 0.425 in [10.8 mm]			
Connectors					

Description	Connector 1	Connector 2		
Туре	N Male	Straight Cut Lead		
Configuration	Straight	Straight		
Impedance	50 Ohms	0 Ohms		
Contact Material & Plating	Brass, Gold			
Dielectric Type	PTFE			
Body Material & Plating	Brass, Nickel			

Environmental Specifications

Temperature

Operating Range

-25 to +70 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- N Male
- Straight Cut Lead
- RG-214

Features:

- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






How to Order

Part Number Configuration:

FMC0100214 - xx



Example: FMC0100214-12 = 12 inches long cable FMC0100214-100cm = 100 cm long cable

N Male to Straight Cut Lead Cable RG-214 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: N Male to Straight Cut Lead Cable RG-214 Coax FMC0100214

URL: https://www.fairviewmicrowave.com/n-male-sexless-cable-rg214-coax-fmc0100214-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
N Male to Straight Cut Lead Cable RG-214 Coax	DWG NO FMC0100214			CAGE CODE 3FKR5		
	CAD FILE 101014	SHEET	SCALI	E N/A	SIZE A	5568

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689