

SMA Male to MMCX Plug Cable RG-316 Coax

Electrical Specifications

Description	Min	Тур	Max	Units			
Frequency Range	DC		3	GHz			
VSWR		1.35:1					
Velocity of Propagation		70		%			
Capacitance	3	32 [104.99)]	pF/ft [pF/m]			

0.315 in [8 mm]

RG-316 50 Ohms

Stranded

FEP, Tan

PTFE

Copper, Silver

Silver Plated Copper Braid

0.098 in [2.49 mm]

0.00926 lbs [4.2 g]

Mechanical Specifications

Cable Assembly Diameter

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter

Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male	MMCX Plug	
Configuration	Straight	Straight	
Polarity	Standard	Standard	
Impedance	50 Ohms	50 Ohms	
Contact Material & Plating	Brass, Gold	Brass, Gold	
Contact Plating Spec.	50µ in. minimum	30µ in. minimum	
Dielectric Type	PTFE	PTFE	
Hex Size	5/16 inch		
Torque	4 in-lbs [0.45 Nm]		
Body Material & Plating	Brass, Nickel	Brass, Gold	
Body Plating Spec.	100µ in. minimum	3µ in. minimum	

Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



FMC0209315



Configuration:


SMA Male

- MMCX Plug
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com







SMA Male to MMCX Plug Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to MMCX Plug Cable RG-316 Coax FMC0209315


URL: https://www.fairviewmicrowave.com/sma-male-mmcx-male-cable-rg316-coax-fmc0209315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Male to MMCX Plug Cable RG-316 Coax	dwg no FMC0209315			CAGE CODE 3FKR5		
/	CAD FILE 101514	SHEET	SCALE	N/A	SIZE A	5568

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689