

SMA Male (Plug) to SMA Male (Plug) Cable RG-223 Coax Up To 11 GHz in 36 Inch

The SMA male to SMA male cable using RG223 coax, part number FMC0202223-36, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible RG-223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0202223-36 SMA male to SMA male cable assembly operates to 11 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	yp Max	Units
Frequency Range	DC		11	GHz
VSWR			1.5:1	
Velocity of Propagation		6	6	%
Capacitance	3	80.94 [[101.51]	pF/ft [pF/m]

Mechanical Specifications

Cable Assembly Length*

Diameter Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

0 in [0 mm] 0 in [0 mm] 0.13 lbs [58.97 g]

RG-223 50 Ohms Solid Copper, Silver PE 2 Silver Plated Copper Braid Silver Plated Copper Braid PVC, Black 0.209 in [5.31 mm]



FMC0202223-36 **DATA SHEET**

Configuration:

- SMA Male
- SMA Male
- RG-223

Features:

- Max Frequency 11 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

Fairview Microwave

an INFINIT[©] brand



Connectors

Description	Connector 1	Connector 2	_
Туре	SMA Male	SMA Male	-
Configuration	Straight	Straight	_
Impedance	50 Ohms	50 Ohms	_
Contact Material & Plating	Brass, Gold	Brass, Gold	_
Contact Plating Spec.	50µ in. minimum	50µ in. minimum	_
Dielectric Type	Teflon	Teflon	_
Body Material & Plating	Brass, Gold	Brass, Gold	_
Body Plating Spec.	3µ in. minimum	3µ in. minimum	-
Hex Size	5/16 inch	5/16 inch	
Torque	4 in-lbs 0.45 Nm	4 in-lbs 0.45 Nm	_
Compliance Certification Plotted and Other Data Notes:	ons (see product page for c	current document)	
low to Order			
Part Number Configurati	ion: FMCC	0202223 - xx (uu cm = Centimeters <blank> = Inches Length</blank>
	3-12 = 12 inches long cable 3-100cm = 100 cm long cal		

SMA Male (Plug) to SMA Male (Plug) Cable RG-223 Coax Up To 11 GHz in 36 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male (Plug) to SMA Male (Plug) Cable RG-223 Coax Up To 11 GHz in 36 Inch FMC0202223-36


URL: https://www.fairviewmicrowave.com/sma-male-sma-male-cable-rg223-coax-fmc0202223-36-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT[©] brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689