

FMC0217315LF DATA SHEET

SMA Male to RA MCX Plug Cable RG-316 Coax with LF Solder

The SMA male to RA MCX plug cable using RG-316 coax, part number FMC0217315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to MCX cable assembly has a male to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0217315LF SMA male to MCX plug cable assembly operates to 3 GHz. The right angle MCX interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Min	Т	ур	Max	U	nits
DC			3		GHz
			1.35:1		
	-	70			%
	32 [1	04.99]	pF/fl	[pF/m]
		DC	DC 70	DC 3 1.35:1	DC 3 1.35:1 70

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm]

Cable Type Impedance Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 50 Ohms Solid Copper, Silver PTFE 1

Silver Plated Copper Braid

FEP, Tan

RG-316

0.098 in [2.49 mm]



Configuration:

- SMA Male
- MCX Plug Right Angle
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2		
Туре	SMA Male	MCX Plug		
Configuration	Straight	Right Angle		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Gold	Brass, Gold		
Contact Plating Spec.	50μ in. minimum	30μ in. minimum		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Nickel	Brass, Gold		
Body Plating Spec.	100μ in. minimum	3μ in. minimum		
Hex Size	5/16 inch			
Torque	4 in-lbs 0.45 Nm			

Environmental Specifications

Temperature


Operating Range -65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order



SMA Male to RA MCX Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to RA MCX Plug Cable RG-316 Coax with LF Solder FMC0217315LF


URL: https://www.fairviewmicrowave.com/standard-sma-male-ra-mcx-plug-cable-rg316-coax-fmc0217315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Male to RA MCX Plug Cable RG-316 Coax with LF Solder	FMC0217315LF			CAGE CODE 3FKR5		
	CAD FILE 101614	SHEET	SCALE	N/A	SIZE A	5568