

TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch



FMC0315400-72

Configuration

- Connector 1: TNC Male
- Connector 2: 7/16 DIN Male
- Cable Type: LMR-400
- Coax Flex Type: Flexible

Features

- Max Frequency 2.5 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- PE Jacket

Applications

- General Purpose
- Laboratory Use

Description

The TNC male to 7/16 DIN male 72 inch cable using LMR-400 coax, part number FMC0315400-72, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0315400-72 TNC male to 7/16 DIN male cable assembly operates to 2.5 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2.5	GHz
Velocity of Propagation		85		%
RF Shielding	90			dB
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.4375 in [11.11 mm]
Weight	0.553 lbs [250.84 g]

TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch



FMC0315400-72

Cable

Cable Type	LMR-400
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	1
Shield Layer 1	Tinned Copper
Shield Layer 2	Aluminum Tape
Jacket Material	PE, Black
Jacket Diameter	0.405 in [10.29 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male	7/16 DIN Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Nickel	Brass, Tri-Metal

Environmental Specifications

Operating Range Temperature	-40 to +85 deg C
-----------------------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch



FMC0315400-72

Typical Performance Data

How to Order



Example: FMC0315400-12 = 12 inches long cable
FMC0315400-100cm = 100 cm long cable

TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch FMC0315400-72](https://www.fairviewmicrowave.com/tnc-male-7-16-male-cable-times-lmr-400-coax-fmc0315400-72-p.aspx)

URL: <https://www.fairviewmicrowave.com/tnc-male-7-16-male-cable-times-lmr-400-coax-fmc0315400-72-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMC0315400-72 CAD Drawing

TNC Male to 7/16 DIN Male Cable LMR-400 Coax in 72 Inch

