

FMC0418315LF DATA SHEET

RA SMA Male to SMC Plug Cable RG-316 Coax with LF Solder

The RA SMA male to SMC plug cable using RG-316 coax, part number FMC0418315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMC cable assembly has a male to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0418315LF SMA male to SMC plug cable assembly operates to 3 GHz. The right angle SMA interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			3		GHz
VSWR				1.35:1		
Velocity of Propagation			70			%
Capacitance		32 [1	04.99	9]	pF/f	t [pF/m]

Mechanical Specifications

Cable Assembly Length*	0 in [0 mm]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter	RG-316 50 Ohms Stranded Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]



Configuration:

- SMA Male Right Angle
- SMC Plug
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[©] brand



Connectors

Description	Connect	or 1	Connecto	or 2	
Туре	SMA Ma	ale	SMC Plu	ıg	
Impedance	50 Ohn	ns	50 Ohm	าร	
Contact Material & Plating	Brass, G	old	Beryllium Copp	oer, Gol	d
Contact Plating Spec.	50µ in. min	imum	50µ in. mini	mum	
Dielectric Type	PTFE		PTFE		
Body Material & Plating	Brass, Ni	ckel	Brass, Go	old	
Body Plating Spec.	100µ in. mir	nimum	3µ in. minir	num	
Hex Size	5/16 in	ch	1/4 inc	h	
Environmental Specifi Temperature	cations				
Operating Range		-65	to +165 deg C		
Compliance Certificati	ons (see product p	bage f	or current docume	nt)	
Plotted and Other Dat	а				
Notes:					
How to Order					
Part Number Configurat	tion:	FMC	0418315LF -	xx	uu
					_
Example: FMC041831	15LF-12 = 12 inche	s long	g cable		
FMC041831	15LF-100cm = 100	cm lo	ng cable		

RA SMA Male to SMC Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA SMA Male to SMC Plug Cable RG-316 Coax with LF Solder FMC0418315LF


URL: https://www.fairviewmicrowave.com/standard-ra-sma-male-smc-plug-cable-rg316-coax-fmc0418315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TH 3. DIMENSIONS ARE IN INCHES [mm].				NY TIME.	
RA SMA Male to SMC Plug Cable RG-316 Coax with LF			CAGE CODE 3FKR5			
Solder	CAD FILE 102114	SHEET	SCAL	E N/A	SIZE A	5568

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689