

FMC0714315-XX DATA SHEET

MCX Plug to RA 10-32 Male Cable RG-316 Coax

Electrical Specifications

Frequency Range DC to 3 GHz Impedance 50 Ohms Velocity of Propagation 70 %

Mechanical Specifications

Temperature

Temperature Operating Range -55 to +155 deg C

Size

Diameter 0.53 in [13.46 mm]

Cable Color Black

Cable

RG-316
Solid
Copper, Silver
1
PTFE
FEP
0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2	
Туре	MCX Plug	10-32 Male Right Angle	
Configuration	Straight	Right Angle	
Inner Conductor Material & Pla	ating Brass, Gold	Brass, Gold	
Inner Conductor Plating Spec.	30µ" Minimum	MIL-G-45204	
Body Material & Plating	Brass, Gold	Brass, Nickel	
Body Plating Spec.	3µ" Minimum		
Dielectric Type	Teflon	Teflon	

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Notes:

- Values at +25 °C, sea level
- RA 10-32 Male to MCX Plug Cables

M. Micro

Configuration:

- MCX Plug
- 10-32 Male Right Angle
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com




FMC0714315-12 = 12 inches long cable

FMC0714315-100cm = 100 cm long cable



Typical Performance Data

Example:



MCX Plug to RA 10-32 Male Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: MCX Plug to RA 10-32 Male Cable RG-316 Coax FMC0714315-

URL: http://www.fairviewmicrowave.com/mcx-male-ra-10-32-male-cable-rg316-coax-fmc0714315-xx-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2015

REV Page 2 of 3





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
MCX Plug to RA 10-32 Male Cable RG-316 Coax	DWG NO FMC0714315-XX			CAGE CODE 3FKR5		
	CAD FILE 102114	SHEET	SCALE	N/A	SIZE A	5568