

FMC0714315LF DATA SHEET

MCX Plug to RA 10-32 Male Cable RG-316 Coax with LF Solder

The MCX plug to RA 10-32 male cable using RG-316 coax, part number FMC0714315LF, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to 10-32 cable assembly has a plug to male gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0714315LF MCX plug to 10-32 male cable assembly operates to 3 GHz. The right angle 10-32 interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			3		GHz
VSWR				1.35:1		
Velocity of Propagation		7	70			%
Capacitance		32 [1	04.99	9]	pF/f	t [pF/m]

Mechanical Specifications

Cable Assembly Length*	0 in [0 mm]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter	RG-316 50 Ohms Stranded Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2
Туре	MCX Plug	10-32 Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Brass, Gold
Contact Plating Spec.	30µ" Min	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Brass, Nickel
Body Plating Spec.	3µ" Minimum	



Configuration:

- MCX Plug
- 10-32 Male Right Angle
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

-55 to +155 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

How to Order

Part Number Configuration:		FM	C0714315LF	-	XX	uu		
							I	cm = Centimeters <blank> = Inches Length</blank>
Example:		15LF-12 = 12 inche 15LF-100cm = 100						

MCX Plug to RA 10-32 Male Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: MCX Plug to RA 10-32 Male Cable RG-316 Coax with LF Solder FMC0714315LF

URL: https://www.fairviewmicrowave.com/standard-mcx-plug-ra-10-32-male-cable-rg316-coax-fmc0714315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
TITLE MCX Plug to RA 10-32 Male Cable RG-316 Coax with	DWG NO FMC0714315LF				CAGE CODE 3FKR5			
LF Solder	CAD FILE 102114	SHEET	SCAL	E N/A	SIZE A	5568		

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689