

FMC0926315 DATA SHEET

MMCX Plug to RA SMB Plug Cable RG-316 Coax

Electrical Specifications

| Description | Min | Min Typ | | Units | |
|-------------------------|-----|-------------|---|-------|--|
| Frequency Range | DC | | 3 | GHz | |
| Velocity of Propagation | | % | | | |
| Capacitance | 3 | 32 [104.99] | | | |

Mechanical Specifications Cable Assembly

Weight 0.01278 lbs [5.8 g]

Cable

Cable Type RG-316
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter PTFE
1
Silver Plated Copper Tape
Silver Plated Copper Braid
FEP, Tan
0.098 in [2.49 mm]

Connectors

| Description | Connector 1 | Connector 2 | | |
|----------------------------|-----------------|------------------------|--|--|
| Туре | MMCX Plug | SMB Plug | | |
| Polarity | Standard | Standard | | |
| Impedance | 50 Ohms | 50 Ohms | | |
| Contact Material & Plating | Brass, Gold | Beryllium Copper, Gold | | |
| Contact Plating Spec. | 30µ in. minimum | 30µ in. minimum | | |
| Dielectric Type | Teflon | Teflon | | |
| Body Material & Plating | Brass, Gold | Brass, Gold | | |
| Body Plating Spec. | 3μ in. minimum | 3μ in. minimum | | |
| | | | | |

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- MMCX Plug
- SMB Plug Right Angle
- RG-316

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Length

Typical Performance Data



Example: FMC0926315-12 = 12 inches long cable FMC0926315-100cm = 100 cm long cable

MMCX Plug to RA SMB Plug Cable RG-316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: MMCX Plug to RA SMB Plug Cable RG-316 Coax FMC0926315

URL: https://www.fairviewmicrowave.com/mmcx-male-ra-smb-plug-cable-rg316-coax-fmc0926315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | |
|---|---|-------|---------|-----------------|--------|------|
| MMCX Plug to RA SMB Plug Cable RG-316 Coax | DWG NO FMC0926315 | | | CAGE CODE 3FKR5 | | |
| | CAD FILE 102814 | SHEET | SCALE N | N/A | SIZE A | 5568 |