

### FMC1818315LF DATA SHEET

## SMC Plug to SMC Plug Cable RG-316 Coax with LF Solder

The SMC plug to SMC plug cable using RG-316 coax, part number FMC1818315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMC to SMC cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1818315LF SMC plug to SMC plug cable assembly operates to 2 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### **Electrical Specifications**

Description	Min	T	ур Мах	Units
Frequency Range	DC		2	GHz
VSWR			1.35:1	
Velocity of Propagation		7	70	%
Capacitance		32 [1	04.99]	pF/ft [pF/m]

#### **Mechanical Specifications**

#### **Cable Assembly**

Length\* Weight

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material

Jacket Diameter

0 in [0 mm] 0.027 lbs [12.25 g]

RG-316 50 Ohms Solid Copper, Silver

PTFE

Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Tan

0.098 in [2.49 mm]



#### **Configuration:**

- SMC Plug
- SMC Plug
- RG-316

#### **Features:**

- Max Frequency 2 GHz
- 70% Phase Velocity
- FEP Jacket

#### **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Connectors**

Description Connector 1		Connector 2				
Туре	SMC Plug	SMC Plug				
Impedance	50 Ohms	50 Ohms				
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold				
Contact Plating Spec.	50μ in. minimum	50μ in. minimum				
Dielectric Type	PTFE	PTFE				
Body Material & Plating	Brass, Gold	Brass, Gold				
Body Plating Spec.	3μ in. minimum	3μ in. minimum				
Hex Size	e 1/4 inch					

#### **Environmental Specifications**

**Temperature** 

Operating Range -65 to +165 deg C

**Compliance Certifications** (see product page for current document)

# Plotted and Other Data Notes: How to Order

Part Number Configuration:

FMC1818315LF - xx uu | cm = Centimeters | chlank > = Inches | Length

Example: FMC1818315LF-12 = 12 inches long cable FMC1818315LF-100cm = 100 cm long cable

SMC Plug to SMC Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMC Plug to SMC Plug Cable RG-316 Coax with LF Solder FMC1818315LF


URL: https://www.fairviewmicrowave.com/smc-plug-smc-plug-cable-rg316-coax-fmc1818315lf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.  ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].						
SMC Plug to SMC Plug Cable RG-316 Coax with LF Solder	DWG NO FMC1818315LF			CAGE CODE 3FKR5			
	CAD FILE 052417	SHEET	SCALE	E N/A	SIZE A	2233	