

# FMC2125085 **DATA SHEET**

# RA SMP Female to Mini SMP Female Cable FM-F086 Coax

#### **Electrical Specifications**

Description	Min Typ		Max	Units		
Frequency Range	DC		18	GHz		
VSWR			1.35:1			

#### **Mechanical Specifications**

### **Cable Assembly**

0.00132 lbs [0.6 g] Weight

#### Cable

Cable Type Impedance Inner Conductor Type Solid Inner Conductor Material and Plating Dielectric Type PTFE Number of Shields

Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter FM-F086 50 Ohms

Copper, Silver

Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Blue

0.104 in [2.64 mm]

#### **Connectors**

Description	Connector 1	Connector 2
Туре	SMP Female	Mini SMP Female
Polarity	Standard	Standard
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Spec.	MIL-G-45204	MIL-G-45204

# **Environmental Specifications**

**Temperature** 

Operating Range -65 to +165 deg C

**Compliance Certifications** (visit www.FairviewMicrowave.com for current document)

#### **Plotted and Other Data**

Notes:



# **Configuration:**

- SMP Female Right Angle
- Mini SMP Female
- FM-F086

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






- Length

#### **Typical Performance Data**

selection in the industry.



RA SMP Female to Mini SMP Female Cable FM-F086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest

Click the following link to obtain additional part information: RA SMP Female to Mini SMP Female Cable FM-F086 Coax FMC2125085


URL: http://www.fairviewmicrowave.com/ra-smp-female-mini-smp-female-cable-hs086-coax-fmc2125085-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

FMC2125085-12 = 12 inches long cable FMC2125085-100cm = 100 cm long cable







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
RA SMP Female to Mini SMP Female Cable FM-F086 Coax	FMC2125085-XX			CAGE CODE 3FKR5		
	CAD FILE 103114	SHEET	SCALE	N/A	SIZE A	5568