

FMC2225085 DATA SHEET

SMP Female to Mini SMP Female Cable FM-F086 Coax

Electrical Specifications

Min	Тур	Max	Units			
DC		18	GHz			
	1.5:1					
	70.6		%			
28.95 [94.98] pF/ft [pF		28.95 [94.98]				
	DC	DC 70.6	DC 18 1.5:1 70.6			

Mechanical Specifications

Cable Assembly

Weight 0.00088 lbs [0.4 g]

Cable

Cable Type FM-F086
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Sil

Dielectric Type
Number of Shields

Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter Copper, Silver
PTFE
2
Silver Plated Copper Tape
Silver Plated Copper Braid
FEP, Blue

0.104 in [2.64 mm]

Connectors

Connector 1	Connector 2	
SMP Female	Mini SMP Female	
Standard	Standard	
50 Ohms	50 Ohms	
Beryllium Copper, Gold	Beryllium Copper, Gold	
30μ in. minimum	MIL-G-45204	
PTFE	PTFE	
Beryllium Copper, Gold	Beryllium Copper, Gold	
30µ in. minimum	MIL-G-45204	
	SMP Female Standard 50 Ohms Beryllium Copper, Gold 30µ in. minimum PTFE Beryllium Copper, Gold	

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:



Configuration:

- SMP Female
- Mini SMP Female
- FM-F086

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






dank> = Inches

Length

Typical Performance Data



Example: FMC2225085-12 = 12 inches long cable

FMC2225085-100cm = 100 cm long cable

SMP Female to Mini SMP Female Cable FM-F086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: SMP Female to Mini SMP Female Cable FM-F086 Coax FMC2225085

URL: http://www.fairviewmicrowave.com/smp-female-mini-smp-female-cable-hs086-coax-fmc2225085-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
TITILE SMP Female to Mini SMP Female Cable FM-F086 Coax	DWG NO FMC2222085			CAGE CODE 3FKR5			
	CAD FILE 103114	SHEET	SCALE	N/A	SIZE A	5568	