

FMCA1222LF **DATA SHEET**

2.92mm Male to 2.92mm Male Cable FM-F086HP Coax with LF Solder

The 2.92mm male to 2.92mm male cable using FM-F086HP coax, part number FMCA1222LF, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-F086HP coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1222LF 2.92mm male to 2.92mm male cable assembly operates to 40 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Jnits
Frequency Range	DC			40		GHz
VSWR				1.5:1		
Velocity of Propagation		76			%	
Capacitance		27 [88.58]		pF/f	pF/ft [pF/m]	

Mechanical Specifications

Cable Assembly

Length* Weight

Cable

Cable Type **Impedance** Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

0 in [0 mm] 0.0194 lbs [8.8 g]

FM-F086HP 50 Ohms Solid

Copper, Silver

PTFE

Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Blue

0.105 in [2.67 mm]



Configuration:

- 2.92mm Male
- 2.92mm Male
- FM-F086HP

Features:

- Max Frequency 40 GHz
- 76% Phase Velocity
- Double Shielded
- FEP Jacket
- 500 Mating Cycles

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

Description	Connector 1	Connector 2			
Туре	2.92mm Male	2.92mm Male			
Impedance	50 Ohms	50 Ohms			
Mating Cycles	500	500			
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold			
Contact Plating Spec.	50μ in. minimum	50μ in. minimum			
Body Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold			
Body Plating Spec.	50μ in. minimum	50μ in. minimum			
Coupling Nut Material & Plat	ing Passivated Stainless Steel	Passivated Stainless Steel			
Hex Size	5/16 inch	5/16 inch			
Torque	8 in-lbs 0.9 Nm	8 in-lbs 0.9 Nm			

Environmental Specifications

Temperature


Operating Range -65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order



2.92mm Male to 2.92mm Male Cable FM-F086HP Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 2.92mm Male to 2.92mm Male Cable FM-F086HP Coax with LF Solder FMCA1222LF


URL: https://www.fairviewmicrowave.com/standard-2.92mm-male-2.92mm-male-cable-fmf086hp-coax-fmca1222lf-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
2.92mm Male to 2.92mm Male Cable FM-F086HP Coax with LF Solder	DWG NO FMCA1222LF			CAGE CODE 3FKR5			
	CAD FILE 103114	SHEET	SCALE	E N/A	SIZE A	5568	