

Water Blue FAKRA Plug to FAKRA Jack Right Angle Cable Using RG174 Coax

The FAKRA plug to RA FAKRA jack cable using RG174 coax, part number FMCA1353Z, from Fairview Microwave is in-stock and ships same day. This Fairview FAKRA to FAKRA cable assembly has a plug to jack gender configuration with 50 ohm flexible RG174 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1353Z FAKRA plug to FAKRA jack cable assembly operates to 1 GHz. The right angle FAKRA interface on the RG174 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Тур	Max	Units	
Frequency Range	DC		1,000	MHz	
VSWR			1.4:1		
Velocity of Propagation		66		%	
Capacitance		30.8 [101.05]		pF/ft [pF/m]	

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.41	0.62	0.8 <mark>85</mark>	1.258	1.8	dB/ft
	1.35	2.03	2.9	4.13	5.91	dB/m

FMCA1353Z DATA SHEET

Configuration:

- FAKRA Plug
- FAKRA Jack Right Angle
- RG174

Features:

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Mechanical Specifications

Cable Assembly

Diameter

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 0.37 in [9.4 mm] 0.024 lbs [10.89 g]

RG174 50 Ohms Stranded Copper Clad Steel PE (LD) 1 Tinned Copper Braid PVC, Black 0.1 in [2.54 mm]

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[®] brand



Connectors

Description	Connector 1	Connector 2	-
Туре	FAKRA Plug	FAKRA Jack	
Configuration	Straight	Right Angle	-
Impedance	50 Ohms	50 Ohms	-
Contact Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold	-
Dielectric Type	Teflon	Teflon	-
Outer Cond Material & Plating	Brass, Nickel	Brass, Nickel	-
Body Material & Plating	Plastic, Paint	Plastic, Paint	-
Mechanical Specification No	otes:		
*All cable assemblies have		5% or \pm 3/8", whichever	r is greater.
operating Range operating Range ompliance Certifications otted and Other Data Notes: • Values at 25°C, sea level.	-40 to -	+80 deg C current document)	
ow to Order			
Part Number Configuration:	FMO	CA1353Z - xx u	cm = Centimeters <blank> = Inches Length</blank>
	= 12 inches long cable 0cm = 100 cm long cab	le	

Water Blue FAKRA Plug to FAKRA Jack Right Angle Cable Using RG174 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Water Blue FAKRA Plug to FAKRA Jack Right Angle Cable Using RG174 Coax FMCA1353Z


URL: https://www.fairviewmicrowave.com/fakra-plug-ra-fakra-jack-cable-rg174-coax-fmca1353z-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







an INFINIT [®] brand	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Water Blue FAKRA Plug to FAKRA Jack Right Angle Cable Using RG174 Coax	DWG NO FMCA1353Z			CAGE CODE 3FKR5		
	CAD FILE 09/21/19	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689