



Snap-On RA MMBX Plug to N Female Bulkhead Cable RG316 Coax

Fairview Microwave's MMBX cable assemblies are part of our full line of RF interconnects available for same-day shipping. These MMBX cable assemblies are designed for test applications or connection of your MMBX system components. With a high frequency range up to 3 GHz, this family of MMBX cables can also be used to connect your panels to PCB's with between series options like MMBX-to-SMA, MMBX-to-N or MMBX-to-TNC assemblies. There are hundreds of possible cable assembly configurations to choose from, all available same day.

This MMBX cable assembly datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave not only has many MMBX cable assembly options, but also a wide selection of RF, microwave and millimeter wave cable assemblies which allows RF designers to customize their configurations to whatever is required. Whether the need is to provide an I/O for a board design or simply create a custom cable assembly configuration, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom RF cable assemblies for you and ship same day.

Electrical Specifications

Description	Min	Т	ур	Max	ι	Inits	
Frequency Range	DC		3			GHz	
VSWR				1.4:1			
Return Loss		-15.56			dB		
Velocity of Propagation		69				%	
Jacket Spark				2,000	\	/rms	

Performance by Frequency

Description F1		F2 F3		F4	F5	Units	
Frequency	0.1	0.25	0.5	1	3	GHz	
Insertion Loss (Max.)	0.11	0.16	0.27	0.38	0.58	dB/ft	
	0.36	0.52	0.89	1.25	1.9	dB/m	

dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.807 in [20.5 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields

RG316 50 Ohms Stranded Copper Clad Steel, Silver PTFE 1



Configuration:

- Snap-On MMBX Plug Right Angle
- N Female Bulkhead
- RG316


Features:

- Max. Operating Frequency of 3 GHz
- Snap-On mating

Applications:

- General Purpose MMBX Test
- PCB Testing
- Low Profile MMBX Cable Jumpers
- PCB-to-Panel Connection

Cable Diagram:



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shield Layer 1 Jacket Material Jacket Diameter Silver Plated Copper Braid FEP, Tan 0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2
Туре	MMBX Plug	N Female
Mount Method		Bulkhead
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Connection Method	Snap-On	
Mating Cycles	100	100
Contact Material & Plating	Beryllium Copper, Go	old Brass, Gold
Contact Plating Spec.		30 µin minimum
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plati	ng Brass, Gold	
Body Material & Plating	Brass, Gold	Brass, Nickel
Body Plating Spec.		100 µin minimum

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Example: FMCA1424-12 = 12 inches long cable

FMCA1424-100cm = 100 cm long cable

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.






Snap-On RA MMBX Plug to N Female Bulkhead Cable RG316 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Snap-On RA MMBX Plug to N Female Bulkhead Cable RG316 Coax FMCA1424

URL: https://www.fairviewmicrowave.com/ra-mmbx-plug-n-female-cable-rg316u-coax-fmca1424-p.aspx







-	FAIRVIEW MICROWAVE INC. LLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
TI	ITLE	FMCA1424				CAGE CODE 3FKR5		
	Snap-On RA MMBX Plug to N Female Bulkhead Cable RG316 Coax	CAD FILE 062217	SHEET 1 OF 1	SCAL	E N/A	SIZE A	9999	