

FMCN1101 DATA SHEET

Right Angle QN Male (Plug) Snap-On Connector For LMR-400, LMR-400-DB Cable, Crimp/Solder

RA QN male snap-on connector with crimp/solder attachment for LMR-400 and LMR-400-DB, part number FMCN1101, from Fairview Microwave is in-stock and ships same day. This QN male connector operates up to a maximum frequency of 6 GHz and offers good VSWR of 1.5:1. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA QN male connector FMCN1101 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Operating Voltage (AC)			500	Vrms
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms
-				

Mechanical Specifications

SIZE	
Length	1.43 in [36.32 mm]
Width/Dia.	0.75 in [19.05 mm]
Height	1.28 in [32.51 mm]
Weight	0.0885 lbs [40.14 g]
Mating Cycles	100 Cycles

Material Specifications

Description	Material	Plating		
Contact	Brass	Silver		
Insulation	PTFE			
Body	Brass	Silver		
Coupling Nut	Brass	Tri-Metal		



Configuration:

- · Snap-On QN Male Connector
- 50 Ohms
- Right Angle Body Geometry
- LMR-400, LMR-400-DB Interface Type
- Crimp/Solder Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.5:1
- · Silver Plated Brass Contact

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications Temperature

Operating Range Hermetic Seal -55 to +125 deg C ATM. cm3/s

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Right Angle QN Male (Plug) Snap-On Connector For LMR-400, LMR-400-DB Cable, Crimp/Solder from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Right Angle QN Male (Plug) Snap-On Connector For LMR-400, LMR-400-DB Cable, Crimp/Solder FMCN1101


URL: https://www.fairviewmicrowave.com/qn-male-snap-on-lmr-400-lmr-400-db-connector-fmcn1101-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689









STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

- 1. STRIP CABLE AS SHOWN & SLIDE FERRULE OVER CABLE.
- INSTALL CABLE INTO BODY OF CONNECTOR AND SOLDER CENTER CONDUCTOR IN PLACE.
- 3. CRIMP FERRULE & SCREW CAP IN PLACE.

CRIMP SIZE REQUIRED

CONTACT: SOLDER

FERRULE: .429" HEX CRIMP TOOL

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Right Angle QN Male (Plug) Snap-On Connector For	DWG NO FMCN1101			CAGE CODE 3FKR5		
LMR-400, LMR-400-DB Cable, Crimp/Solder	CAD FILE 062216	SHEET	SCAL	E N/A	SIZE A	2233

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689