

FMCA1579 DATA SHEET

Slide-On BMA Plug Bulkhead to SMP Female Cable FM-SR086TBJ Coax

The BMA plug slide-on bulkhead to SMP female cable using FM-SR086TBJ coax, part number FMCA1579, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to SMP cable assembly has a plug to female gender configuration with 50 ohm formable FM-SR086TBJ coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The FMCA1579 BMA plug to SMP female cable assembly operates to 18 GHz. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

•						
Description	Min	Т	ур	Max	ι	Inits
Frequency Range	DC			18		GHz
VSWR				1.5:1		
Return Loss				15.56		dB
Velocity of Propagation		69	9.5			%
RF Shielding	100					dB
Group Delay		1.43	[4.69]		ns/f	t [ns/m]
Capacitance		29 [9	95.14]		pF/f	t [pF/m]
DC Resistance Inner Cor	ductor	65.7 [215.55]		Ω/100	0ft [Ω/Km]
DC Resistance Outer Cor	nductor	10.2	[33.46]		Ω/100	0ft [Ω/Km]

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Max.)	0.22	0.33	0.52	0.77	1.13	dB/ft
	0.72	1.08	1.71	2.53	3.71	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly Diameter

0.315 in [8 mm]

Cable Cable Type Impedance

FM-SR086TBJ 50 Ohms



Configuration:

- Slide-On BMA Plug Bulkhead
- SMP Female
- FM-SR086TBJ

Features:

- Max Frequency 18 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Outer Conductor Material and Plating Jacket Material Jacket Diameter Solid Copper Clad Steel, Silver PTFE 1 Tinned Copper Composite Braid FEP, Black 0.105 in [2.67 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius

0.5 in [12.7 mm] 0.787 in [19.99 mm]

Connectors

Description	Connector 1	Connector 2
Туре	BMA Plug	SMP Female
Mount Method	Bulkhead	
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	
Contact Material & Plating	Bronze, Gold	Beryllium Copper, Gold
Contact Plating Spec.	51.18µ in. minimu	m MIL-G-45204
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plati	ing Brass, Tri-Metal	
Outer Cond Plating Spec.	78.74µ in. minimu	m
Body Material & Plating	Brass, Tri-Metal	Beryllium Copper, Gold
Body Plating Spec.	78.74µ in. minimu	m MIL-G-45204
Hex Size	8 mm	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Environmental Specifications

Temperature Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:





Typical Performance Data



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Slide-On BMA Plug Bulkhead to SMP Female Cable FM-SR086TBJ Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Slide-On BMA Plug Bulkhead to SMP Female Cable FM-SR086TBJ Coax FMCA1579


URL: https://www.fairviewmicrowave.com/bma-plug-smp-female-cable-rg405-type-.086-coax-fmca1579-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
Slide-On BMA Plug Bulkhead to SMP Female Cable FM- SR086TBJ Coax	dwg no FMCA1579			CAGE CODE 3FKR5		
	CAD FILE 12/13/17	SHEET	SCAL	.e n/a size a	CN2245	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689