

# FMCN1349Z DATA SHEET

# FAKRA Plug Connector Crimp/Solder Attachment for RG174, RG316, RG188, .100 inch, FM-B100, FM-C100, LMR-100, Water Blue Color

FAKRA plug connector with crimp/solder attachment for RG174, RG316, RG188, .100 inch, FM-B100, FM-C100 and LMR-100, water blue color, part number FMCN1349Z, from Fairview Microwave is in-stock and ships same day. This FAKRA plug connector operates up to a maximum frequency of 4 GHz and offers good VSWR of 1.3:1.

Fairview's FAKRA plug connector FMCN1349Z datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

#### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.3:1	
Operating Voltage (AC)			335	Vrms
DWV (AC)			800	Vrms
Inner Cond. DC Resistance	e		6	mOhms
Outer Cond. DC Resistance	e		2.5	mOhms
Insulation Resistance	1,000			MOhms

#### **Mechanical Specifications**

Size

Length Width/Dia. Height 0.035 in [0.89 mm] 0.37 in [9.40 mm] 0.433 in [11 mm]

#### **Material Specifications**

Description	Material	Plating			
Contact	Phosphor Bronze	Gold			
Insulation	PTFE				
Outer Conductor	Brass	Nickel			
Body	Plastic				

#### **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:



## **Configuration:**

- FAKRA Plug Connector
- 50 Ohms
- Straight Body Geometry
- RG174, RG316, RG188, .100 inch, FM-B100, FM-C100, LMR-100 Interface Type
- Crimp/Solder Attachment

#### Features:

- Operating Frequency of 4 GHz Max.
- Good VSWR of 1.3:1
- Gold Plated Phosphor Bronze Contact

### **Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





FAKRA Plug Connector Crimp/Solder Attachment for RG174, RG316, RG188, .100 inch, FM-B100, FM-C100, LMR-100, Water Blue Color from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: FAKRA Plug Connector Crimp/Solder Attachment for RG174, RG316, RG188, .100 inch, FM-B100, FM-C100, LMR-100, Water Blue Color FMCN1349Z


URL: https://www.fairviewmicrowave.com/fakra-plug-standard-rg174-rg316-connector-fmcn1349z-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







Fairview Microwave	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.							
an INFINIT® brand	3. DIMENSIONS ARE IN INCHES [mm].							
FAKRA Plug Connector Crimp/Solder Attachment for RG174, RG316, RG188, .100 inch, FM-B100, FM-C100, LMR-100, Water Blue Color	DWG NO FMCN1349Z				CAGE CODE 3FKR5			
	CAD FILE 09/22/19	SHEET	1 OF 1	SCAL	E N/A	SIZE A	7361	

.X