



# 2.92mm Male PCB Connector Vertical Launch Clamp Attachment Removable Stripline Launch

2.92mm male connector with clamp attachment for vertical launch PCB, part number FMCN1477, from Fairview Microwave is in-stock and ships same day. This 2.92mm male connector operates up to a maximum frequency of 40 GHz and offers good VSWR of 1.3:1.

Fairview's 2.92mm male connector FMCN1477 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

# **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.3:1	

**Electrical Specification Notes:** 

Actual VSWR performance is largely dependent on circuit board design. For optimal results, the connector and circuit launch geometry should be modeled using Electromagnetic Simulation tools.

#### **Mechanical Specifications**

Size

 Length
 0.5 in [12.7 mm]

 Width/Dia.
 0.315 in [8.00 mm]

 Height
 0.39 in [9.91 mm]

 Weight
 0.011 lbs [4.99 g]

 Mating Cycles
 500 Cycles

### **Material Specifications**

Description	Material	Plating
Contact	Brass	Gold
Insulation	Ultem1000	
Body	Passivated Stainless Steel	
Coupling Nut	Passivated Stainless Steel	

Mechanical Specification Notes: Launch Pin is Gold Plated Beryllium Copper

## **Environmental Specifications**

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



# **Configuration:**

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- Vertical Launch Interface Type
- · Clamp Attachment

## **Features:**

- Operating Frequency of 40 GHz Max.
- Good VSWR of 1.3:1
- · Gold Plated Brass Contact
- Reusable vertical launch installation

# Applications:

- General Purpose Test
- PCB Applications
- Signal Integrity Measurement
- Chip Evaluations
- SERDES
- Vertical Launch Test Fixtures

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com







## **Assembly Instruction**

# STEP 1:

Position vertical launch above substrate.











## **Typical Performance Data**



Test data taken with 2 connectors on both ends of test fixture



Test data taken with 2 connectors on both ends of test fixture






2.92mm Male PCB Connector Vertical Launch Clamp Attachment Removable Stripline Launch from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm Male PCB Connector Vertical Launch Clamp Attachment Removable Stripline Launch FMCN1477

URL: https://www.fairviewmicrowave.com/2.92mm-male-vertical-launch-pcb-connector-fmcn1477-p.aspx







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].				
2.92mm Male PCB Connector Vertical Launch Clamp Attachment Removable Stripline Launch	DWG NO FMCN1477			CAGE CODE 3FKR5	
	CAD FILE 06/04/18	SHEET	SCAL	LE N/A SIZE A	CN2379