

# FMCN45842 DATA SHEET

# 20KV Male Connector Crimp/Solder Attachment for RG214 Cable

The Fairview Microwave FMCN45842 is designed for high voltage applications and is rated to 20KV. This 20KV male connector utilizes crimp/solder attachment for the contact. Our 20KV male coax connector from Fairview Microwave has an interface type of RG214.

The Fairview Microwave 20KV male coaxial connector has a PE (HD) dielectric type. This Fairview Microwave 20KV coax cable connector has a brass body with nickel over copper plating. Our 20KV male connector uses beryllium copper contact with gold over nickel over copper plating material. This 20KV male coax RF connector is RoHS and REACH compliant, you can find this 20KV male coax connector datasheet specifications above.

Fairview Microwave standard straight male 20KV connector will ship the same day. Our 20KV standard straight male high voltage connector is part of over one million RF, microwave, and millimeter wave components in stock and ready for same-day shipment worldwide. We also build custom standard cable assemblies that will ship quickly from our location.



Description	Min	Тур	Max	Units
Operating Voltage (DC)			20,000	Vdc
Test Voltage (DC)			30,000	Vdc
Inner Cond. DC Resistance	е		3	mOhms
Outer Cond. DC Resistance	е		2	mOhms
Insulation Resistance	1,000			MOhms



## **Configuration:**

- 20KV Male Connector
- MIL-STD-202
- Straight Body Geometry
- RG214 Interface Type
- Crimp/Solder Attachment

#### **Features:**

- Gold over nickel over copper Plated Beryllium Copper Contact
- High Density PE Insulator

### **Applications:**

- General Purpose Test
- Custom Cable Assemblies
- High Voltage Pulsed RF Transmission

#### **Mechanical Specifications**

Size

Length Width/Dia. Height Weight 3.9 in [99.06 mm] 0.75 in [19.05 mm] 0.75 in [19.05 mm] 0.018 lbs [8.16 q]

#### **Material Specifications**

Description	Material	Plating	
Contact	Beryllium Copper	Gold over nickel over copper	
Contact Spring		Nickel over Copper	
Insulation	PE (HD)		
Body	Brass	Nickel Over Copper	
Coupling Nut	Brass	Nickel Over Copper	
Gasket	Silicone		
Crimp Sleeve	Brass	Nickel over Copper	
Washer	Brass	Nickel over Copper	

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





# **Environmental Specifications**

**Temperature** 


Operating Range Salt Spray -55 to +85 deg C MIL-STD-202, Method 101, Condiiton B

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **Assembly Instruction**







20KV Male Connector Crimp/Solder Attachment for RG214 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 20KV Male Connector Crimp/Solder Attachment for RG214 Cable FMCN45842

URL: https://www.fairviewmicrowave.com/20kv-male-rg214-connector-fmcn45842-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





