

FMCN45900 DATA SHEET

MHV Female Connector Crimp/Solder Attachment for RG142, RG58, RG141, RG303, .195 inch, LMR-195 Cable

FMCN45900 MHV female coax connector has an interface type of MHV female which is compatible with RG142, RG58, RG141, RG303, .195 inch and LMR-195 cables and has a 50 Ohms impedance. Fairview Microwave's MHV female connector uses crimp/solder as an attachment method.

The Fairview Microwave MHV female coax connector has a PTFE dielectric type. Fairview Microwave's MHV coax connector has a brass body with nickel plating. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings above.

This MHV female RF connector with coax termination is designed to be used with RG142, RG58, RG141, RG303, .195 inch and LMR-195 cables. Our high-quality FMCN45900 connector features a QQ-N-290 body plating specification. This MHV connector has a silver inner contact plating.

This Fairview Microwave female MHV connector will ship the same business day as purchased. Our MHV female connector is part of over 40,000 RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Mechanical Specifications

Size

Length Width/Dia. Height Weight 1.5 in [38.1 mm] 0.5 in [12.70 mm] 0.5 in [12.7 mm] 0.028 lbs [12.7 q]

Material Specifications

·		
Description	Material	Plating
Contact		Silver QQ-S-365
Insulation	PTFE	
Body	Brass	Nickel QQ-N-290

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- MHV Female Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- RG142, RG58, RG141, RG303, .195 inch, LMR-195 Interface

 Type
- Crimp/Solder Attachment

Features:

- Silver Plated Contact
- Contact plating according to QQ-S-365

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






MHV Female Connector Crimp/Solder Attachment for RG142, RG58, RG141, RG303, .195 inch, LMR-195 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: MHV Female Connector Crimp/Solder Attachment for RG142, RG58, RG141, RG303, .195 inch, LMR-195 Cable FMCN45900

URL: https://www.fairviewmicrowave.com/mhv-female-rg142-rg58-rg141-rg303-.195-lmr-195-connector-fmcn45900-p. aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





