

**RF PCB Connector, MCX Jack Right Angle Connector
Solder Attachment Thru Hole PCB, .200 inch x
.052 inch Hole Spacing**

RA MCX jack connector with solder attachment for thru hole PCB (.200 inch x .052 inch hole spacing), part number FMCN44266, from Fairview Microwave is in-stock and ships same day. This MCX jack connector operates up to a maximum frequency of 6 GHz. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA MCX jack connector FMCN44266 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
Operating Voltage (AC)			335	Vrms
DWV (AC)			1,000	Vrms

Performance by Frequency


Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 1	1 to 3				GHz
VSWR, Max	1.5:1	1.63:1				

Mechanical Specifications

Size	
Length	0.394 in [10.01 mm]
Width/Dia.	0.236 in [5.99 mm]
Height	0.374 in [9.5 mm]
Weight	0.006 lbs [2.72 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30μ in. minimum
Insulation	Teflon	
Body	Brass	Gold 3μ in. minimum


Configuration:

- MCX Jack Connector
- CECC 22220
- 50 Ohms
- Right Angle Body Geometry
- Thru Hole Interface Type
- Solder Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Gold Plated Beryllium Copper Contact
- 30μ in. minimum contact plating

Applications:

- General Purpose Test
- PCB Applications

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RF PCB Connector, MCX Jack Right Angle Connector Solder Attachment Thru Hole PCB, .200 inch x .052 inch Hole Spacing from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RF PCB Connector, MCX Jack Right Angle Connector Solder Attachment Thru Hole PCB, .200 inch x .052 inch Hole Spacing FMCN44266](#)

URL: <https://www.fairviewmicrowave.com/mcx-jack-thru-hole-pcb-connector-fmcn44266-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

