

## Reverse Polarity TNC F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 6GHz, 60 V Max., Gas Discharge Tube, Bracket Toward Body

RF surge protector (also known as lightning arrestor) FMSP1073 from Fairview Microwave utilizing a gas discharge tube design to protect critical hardware while maintaining the RF performance. This RF surge protector component is manufactured in a coaxial in-line design with wide operating frequency range. Fairview Microwave RF surge protector products are available in stock with same day shipping.

### Electrical Specifications

Description	Gas Discharge Tube			Units
	Min	Typ	Max	
Surge Protector Type	Gas Discharge Tube			
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Insertion Loss			0.6	dB
Operating Voltage (DC)			60	Volts
Surge Current IEC 61000-4-5 8/20 $\mu$ s		5		kA
Turn On Voltage		90		Volts

### Mechanical Specifications

Size	
Length	2.08 in [52.83 mm]
Width/Diameter	0.906 in [23.01 mm]
Height	1.206 in [30.63 mm]
Weight	0.5 lbs [226.8 g]
Housing Material and Plating	Brass, Nickel
Configuration	
Input Connector	TNC Female Reverse Polarity
Output Connector	TNC Female Reverse Polarity

### Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:



### Features:

- Broadband Performance from DC to 6 GHz
- Repetitive Lightning Strike Capability
- Bi-directional Protection
- Replaceable Gas Tube for Installation Longevity
- Robust Brass Construction

### Applications:

- WiFi
- Wireless Base Stations
- Automotive
- Avionics
- Military Communications

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Reverse Polarity TNC F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 6GHz, 60 V Max., Gas Discharge Tube, Bracket Toward Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Reverse Polarity TNC F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 6GHz, 60 V Max., Gas Discharge Tube, Bracket Toward Body FMSP1073](#)

URL: <https://www.fairviewmicrowave.com/surge-protector-6ghz-gas-discharge-tube-fmsp1073-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



