

FMW12AT002A-30 DATA SHEET

WR-12 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 60 GHz to 90 GHz, UG-387/U Round Cover Flange

Fairview Microwave's Continuously Variable Waveguide Attenuators are offered for the frequency range of 18 to 110 GHz in different waveguide bands. The attenuation value of the Continuously Variable attenuators are from 0 to 30 dB with full waveguide operational bandwidth. The Continuously Variable attenuators are equipped with a micrometer, which enables rapid re-setting. With calibrated charts, attenuators can be used as direct reading attenuator for bench top test set use. The level setting attenuators are typically used in the test setups and prototype assemblies where certain attenuation is required.



Description	Min	Тур	Max	Units
Frequency Range	60		90	GHz
Typical Attenuation Value	0		30	dB
Insertion Loss		0.4		dB
Input Power (CW)			2	Watts
VSWR		1.15:1		

Values at 25°C, sea level

Mechanical Specifications

Flange 1

Interface UG-387/U Material Brass Plating Gold

Waveguide

InterfaceWR-12MaterialCopperPlatingGold

Flange 2

Interface UG-387/U
Material Brass
Plating Gold

Size

 Length
 2.5 in [63.5 mm]

 Width
 1.12 in [28.45 mm]

 Height
 2.164 in [54.97 mm]

 Weight
 0.15 lbs [68.04 q]

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25 °C, sea level



Features:

- 30 dB Attenuation level
- Rotary Dial for Continous Adjustments
- Freguency Range: 60 GHz to 90 GHz
- Typical VSWR 1.15:1
- Max Power Rating: 2 Watts (CW)

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






WR-12 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 60 GHz to 90 GHz, UG-387/U Round Cover Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: WR-12 Waveguide Continuously Variable Attenuator with Dial 0 to 30 dB Operating from 60 GHz to 90 GHz, UG-387/U Round Cover Flange FMW12AT002A-30

URL: https://www.fairviewmicrowave.com/wr-12-waveguide-continuously-variable-attenuator-25-db-ug387-round-fm-w12at002a-30-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689



FMW12AT002A-30 DATA SHEET

