

78 Ohm TRS 3-Lug NI Bulkhead Front Mount Jack 1553 Connector Solder/Solder for TRS 3-Slot Plug

78 Ohm TRS 3-Lug Jack Bulkhead 1553 Bulkhead Connector Solder/Solder Attachment for TRS 3-Slot Plug Cable, part number FMCNMSB00009, from Fairview Microwave is in-stock and ships same day. This TRS 3-Lug jack connector operates up to a maximum frequency of 500 MHz. Fairview's FMCNMSB00009 bulkhead TRS 3-Lug connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Bulkhead TRB Jack Feedthru Connectors are used to connect TRB Plug connectors through a panel. They are available in Isolated and Non-Isolated versions.

Fairview's 78 ohm TRS 3-Lug jack bulkhead connector FMCNMSB00009 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB

Mechanical Specifications

Size	
Length	1.05 in [26.67 mm]
Width/Dia.	0.72 in [18.29 mm]
Height	0.43 in [10.92 mm]
Weight	0.01 lbs [4.54 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel



Configuration:

- TRS 3-Lug Jack Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- TRS 3-Slot Plug Interface Type
- Solder/Solder Attachment
- Bulkhead
- 1553 Design

Features:

- Operating Frequency of 500 MHz Max.
- Gold 30 micro inches Plated Beryllium Copper Contact
- Contact plating according to ASTM-B-488
- Twinax Connectivity
- Bayonet Coupling
- Front Mount

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies
- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

78 Ohm TRS 3-Lug NI Bulkhead Front Mount Jack 1553 Connector Solder/Solder for TRS 3-Slot Plug from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [78 Ohm TRS 3-Lug NI Bulkhead Front Mount Jack 1553 Connector Solder/Solder for TRS 3-Slot Plug FMCNMSB00009](#)

URL: <https://www.fairviewmicrowave.com/trs-3-lug-jack-trs-3-slot-plug-connector-fmcnmsb00009-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



ZONE		REVISION		APPROVED	
A	REV	DESCRIPTION <td>DATE <td>CHANGED BY <td>EKIM</td> </td></td>	DATE <td>CHANGED BY <td>EKIM</td> </td>	CHANGED BY <td>EKIM</td>	EKIM
		INITIAL RELEASE	07/27/2023	SREITER	

<p>Fairview Microwave[®] an INFINIT[®] brand</p> <p>Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678</p>		<p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> <p>SCALE: NONE</p> <p>SHEET: 1 OF 1</p>	
<p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE MILLIMETERS.</p> <p>TOLERANCES:</p> <p>X = ±.2 [5] FRACTIONS ± 1/32</p> <p>.XX = ±.02 [0.5] ANGLES ± 1°</p> <p>.XXX = ±.005 [0.13]</p> <p>CABLE LENGTH TOLERANCES:</p> <p>≤ 12 [305] = ±.1 [25] / -0</p> <p>> 12 [305] ≤ 60 [1524] = ±.2 [5] / -0</p> <p>> 60 [1524] ≤ 300 [7620] = ±.4 [10] / -0</p> <p>> 300 [7620] ≤ 400 [10160] = ±.6 [15] / -0</p> <p>> 400 [10160] ≤ 7620 [192540] = ±.8 [20] / -0</p> <p>> 7620 [192540] = ±1.0 [25] / -0</p>		<p>DESCRIPTION</p> <p>78 OHM TRS 3-LUG NI BULKHEAD FRONT MOUNT JACK 1553 CONNECTOR SOLDER/SOLDER FOR TRS 3-SLOT PLUG</p>	
SIZE	CAGE CODE	ITEM NO.	REV
A	3FKR5	FMCNMSB00009	A

T-Rev D3