

**3-SLOT TRB PLUG 3000 OHM TERMINATOR W 6" CHAIN**
**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Impedance		3,000		Ohms


**Applications:**

- TRB PLUG

**Mechanical Specifications**
**Size**

Length	1.76 in [44.7 mm]
Width	0.56 in [14.22 mm]
Height	0.56 in [14.22 mm]
Weight	0.0625 lbs [28.35 g]

**Configuration**

Connector	TRB 3-Slot Plug
Connector Specification	MIL-STD-1553

**Material Specifications**

Description	Material	Plating
Connector 1 Contact	Bronze	Gold 30 micro inches ASTM-B-488
Gasket	Rubber	
Body	Brass	Nickel ASTM-B-733

**Environmental Specifications**
**Temperature**

Operating Range	-55 to +200 deg C
-----------------	-------------------

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**


Notes:

3-SLOT TRB PLUG 3000 OHM TERMINATOR W 6" CHAIN from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [3-SLOT TRB PLUG 3000 OHM TERMINATOR W 6" CHAIN FMTR10-06403-038](#)

URL: [https://www.fairviewmicrowave.com/3-slot-trb-plug-3000-ohm-terminator-w-6"-chain-fmtr10-06403-038-p.aspx](https://www.fairviewmicrowave.com/3-slot-trb-plug-3000-ohm-terminator-w-6)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

FM DS Rev=04 A382