

FMW06S000-9 DATA SHEET

WR-6 Waveguide Section 9 Inch Straight Length with UG-387/U-Mod Round Cover Flange from 110 GHz to 170 GHz

Fairview's Microwave FMW06S000-9 is a 9 inch WR-6 straight waveguide section that operates from 110 GHz to 170 GHz. This straight waveguide section offers a typical 0.75 dB insertion loss and a typical 1.15 VSWR. The input of this straight waveguide section has a UG-387/U-M Flange. FMW06S000-9 is part of over 40,000 RF, microwave and millimeter wave components. WR-6 straight waveguide section will ship worldwide the same day it is purchased along with our other RF components.

Electrical Specifications*

_				
Description	Min	Тур	Max	Units
Frequency Range	110		170	GHz
VSWR		1.15:1		
Insertion Loss		0.75		dB

^{*} Values at 25°C, sea level

Mechanical Specifications

Waveguide Size WR-6

Section Length 9 in [228.6 mm]

Flange 1

Flange Type Round Cover Flange Designation UG-387/U-Mod

Material Oxygen Free Hard Copper

Plating Gold

Waveguide

Interface WR-6

Material Oxygen Free Hard Copper

Plating Gold

Flange 2

Flange Type Round Cover Flange Designation UG-387/U-Mod

Material Oxygen Free Hard Copper

Plating Gold

Size

Weight 0.05 lbs [22.68 g]

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

· Values at 25 °C, sea level



Features:

- 9" Length
- · WR-6 Waveguide
- UG-387/U-M Flange
- 110 GHz to 170 GHz Frequency Range
- Comprehensive waveguide offering also includes E-Bends, H-Bends, Waveguide to Coax Adapters, Filters, Terminations, and more.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





WR-6 Waveguide Section 9 Inch Straight Length with UG-387/U-Mod Round Cover Flange from 110 GHz to 170 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-6 Waveguide Section 9 Inch Straight Length with UG-387/U-Mod Round Cover Flange from 110 GHz to 170 GHz FMW06S000-9


URL: https://www.fairviewmicrowave.com/wr-6-waveguide-section-straight-ug387-mod-round-fmw06s000-9-p.aspx











■■■ Fairview Microwave NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.

2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.

3. DIMENSIONS ARE IN INCHES [mm]. an INFINIT® brand TITLE DWG NO CAGE CODE FMW06S000-9 3FKR5 WR-6 Waveguide Section 9 Inch Straight Length with UG-387/U-Mod Round Cover Flange from 110 GHz to 170 GHz CAD FILE 08/05/19 SCALE N/A SIZE A 1 OF 1 7361